TYPE APPROVAL CERTIFICATE

Certificate no.:
TAE0000440
Revision No:
1

This is to certify:

that the Low Voltage Cable

with type designation(s)
EXZHELLENT MAR RDt, EXZHELLENT MAR RO1Dt, EXZHELLENT MAR RO2Dt

issued to
Grupo General Cable Sistemas, S.L.
Abrera, Barcelona, Spain

is found to comply with
DNV rules for classification – Ships, offshore units, and high speed and light craft

Application:

Control and instrumentation.
Products approved by this certificate are accepted for installation on all vessels classed by DNV.

Type	Rated voltage (V)	Temp. class (°C)
EXZHELLENT MAR RDt	150/250	90
EXZHELLENT MAR RO1Dt	150/250	90
EXZHELLENT MAR RO2Dt	150/250	90

Issued at **Høvik** on **2026-10-05**

This Certificate is valid until **2030-11-29**.
DNV local unit: **Area NB/CMC Iberia**

Approval Engineer: **Deep Vaishampayan**

for **DNV**

This document has been digitally signed and will therefore not have handwritten signature

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid.
The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to USD 300 000.

Product description

EXZHELLENT MAR RDt,
EXZHELLENT MAR RO1Dt,
EXZHELLENT MAR RO2Dt

Construction:

Conductors:	Plain or tinned, stranded copper Class 2 or class 5
Core insulation:	HF XLPE
Screen:	Individual or common screen of AL/PE tape with tinned copper drain wire. O1=Individual screen O2=Overall screen
Inner covering:	Tape or Halogen free compound
Outer sheath:	SHF1

No of Elements:	Cross sectional area [mm^2]
2, 3, 4, 5, 7, 10, 12, 14, 16, 19, 24, 27 single cores	1,0 1,5 2,5
1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 22, 23, 24 pairs	0,75 1,0 1,5
1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16 triples	0,75 1,0 1,5

Manufactured by

Production site: Santa Perpetua Plant -Poligon Industrial
Can Vinyalets 2 - 08130 Santa Perpetua de Mogoda, Barcelona, Spain

Application/Limitation

The requirements of SOLAS Amendments Chapter II-1, Part D, Reg. 45, 5.2 (provision to be taken to limit Fire Propagation along Bunches of Cables or Wires) are fulfilled without any additional measures.

Type Approval documentation

Data sheets: General Cable EXZHELLENT MAR RO1Dt 150/250V Cu5 Rev4 5-Feb-2020
Dimensional data sheet AFUMEX NAU XA 250 V Rev. 00 dated 10/08
Dimensional data sheet AFUMEX NAU XHA 250 V and NAU XOA 250 V
Test reports: DET-01/0808 dated March 2008
DI 5952 dated 2008-11-28
DI 5953 dated 2008-11-28

Tests carried out

	Release	General description	Limitation
DNV-CP-0399	2021-08	Class Programme Electric cables	
IEC 60092-350	2020-01	Electrical installations in ships - Part 350: General construction and test methods of power, control and instrumentation cables for shipboard and offshore applications	
IEC 60092-360	2021-01	Electrical installations in ships - Part 360: Insulating and sheathing materials for shipboard and offshore units, power, control, instrumentation and telecommunication cables.	
IEC 60092-376	2025-04	Electrical installations in ships - Part 376: Cables for control and instrumentation circuits 150/250 V (300 V)	
IEC 60332-1-2	2025-06	Tests on electric and optical fibre cables under fire conditions - Part 1-2: Test for vertical flame propagation for a single insulated wire or cable - Procedure for 1 kW pre-mixed flame	Flame retardant small scale. Distance between the lower edge of the top support and the onset of charring > 50 mm and Charring not to extend downwards > 540 mm from the lower edge of the top support.

	Release	General description	Limitation
IEC 60332-3-22	2018-07	Tests on electric cables under fire conditions - Part 3-22: Test for vertical flame spread of vertically-mounted bunched wires or cables - Category A	Charred portion of sample does not exceed 2,5m above bottom edge of burner.
IEC 60754-1	2019-11	Test on gases evolved during combustion of materials from cables - Part 1: Determination of the halogen acid gas content	Low Halogen: <0,5% Halogen
IEC 60754-2	2019-11	Test on gases evolved during combustion of materials from cables - Part 2: Determination of acidity (by pH measurement) and conductivity	Halogen free: pH > 4,3 Conductivity < 10µS/mm
IEC 61034-1/2	2019-11	Measurement of smoke density of cables burning under defined conditions – Part 1: Test apparatus Part 2: Test procedure and requirements	Low smoke Light transmittance ≥60%

Marking of product

GENERAL CABLE SAP - EXZHELLENT MAR RDt or RO1Dt or RO2Dt 150/250V - size – IEC 60092-376 IEC 60332-3-22 - Lot No. [meter marking]

SAP = Santa Perpetua Plant.

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the Type approval are complied with and that no alterations are made to the product design or choice of materials.

The main elements of the assessment are:

- Inspection on factory samples, selected at random from the production line (where practicable)
- Results from Routine tests (RT) and selected type tests (ref. to applicable class programs) checked (if not available these tests shall be carried out)
- Review of type approval documentation
- Review of possible change in design, materials and performance
- Ensuring traceability between manufacturer's product type marking and Type Approval Certificate.

Periodical assessment is to be performed after 2 years and after 3.5 years. A renewal assessment will be performed at renewal of the certificate.

END OF CERTIFICATE